



DIN Bushings

-DIN172A DIN179A-

CAD Data

RoHS

Type		Material	D	Hardness
Shouldered	Straight			
DIN172A	DIN179A	1.0718/ 11SMnPb30	2.5-26	62 +/-2 HRC
		1.7131/ 16MnCr 5	28-35	

$6.3 \sqrt[0.8]{G}$

DIN 172 A

DIN 179 A

All specifications without any tolerance according: JIS B 0405-1991-m (DIN ISO 2768-m)

Part Number	D	D Tolerance	L			d n6	H	R	T	
			Short	Medium	Long					
DIN172A DIN179A	2.5	+0.016	6	9		5	8	1	2	
	3	+0.006				6	9			
	3.3									
	3.5					7	10			
	4					8	11		2.5	
	4.2	+0.022		8	12	16				
	4.5	+0.010								
	5									
	5.5									
	6					10	13	1.5	3	
	6.5									
	6.8			10	16	20				
	7									
	7.5									
	8	+0.028								
	8.5	+0.013								
	9									
	9.5					15	18	2	4	
	10									
	10.2			12	20	25				
	10.5									
	11					18	22			
	12									
	13	+0.034								
	14	+0.016				22	26	3	5	
	15									
	16			16	28	36				
	17					26	30			
	18									
	19									
	20					30	34	3	5	
	22									
	24	+0.041		20	36	45				
	25	+0.020								
	26					35	39			
28										
30					42	46	3	5		
35	+0.050		25	45	56					
	+0.025									
					48	52				



Order Example

Part Number - D - L
 Example DIN179A - D5.5 - L10