


INSIDE ARROWS FOR PL EXCHANGE TYPE

—STANDARD · SHALLOW ARROW MARK TYPE—



Inside arrows for PL exchange type are the same with those of overall length adjustable type.

RoHS

Inside Arrow

No.	F	T	H	B	ℓ	M×P
4				2.4	2.7	M1.6×0.20
5	7.7	1.5	3.0	2.9		
6				3.7		
8	9.7	2.0	3.5	5.0	3.2	M2.3×0.25
10	11.7		4.0	6.3	4.0	M2.5×0.35
12		2.5		7.5	4.2	M3.0×0.35
16	13.7		4.3	11.0	4.8	
20	15.7	3.5	5.0	13.2	5.3	M4.0×0.35

No.	Arrow mark depth (mm)	
	Standard	Shallow
4	0.22	0.12
5	0.25	0.14
6	0.40	0.18
8	0.40	0.20
10~20	0.50	0.22

Compared to the standard type, the inside arrow is difficult to turn, so be careful not to scrape the arrow with the tip of a screwdriver. If the inside arrow is scraped, it may not be possible to remove it.

Inside arrows on this page are adapted for combination with outside rings of date marked pin sets on P.571 and P.579, and products on P.574 and P.580.

SUS420
50~53HRC

Year Type

Indication	Part Number		Year	U/Price 1~9
	Type	No.		
Year	DYYX DYYXU (Shallow arrow)	4	15 for 2015	Quotation
		5	※Days to ship will be 5-days for the adjustment of production after November 2015.	
		6		
		8	16 for 2016 (available from Sept.,2015)	
		10	※Days to ship will be 5-days for the adjustment of production after November 2016.	
		12		
16	17 for 2017 (available from Sept.,2016)			
20	※Days to ship will be 5-days for the adjustment of production after November 2017.			

The inside arrows are the same with those of overall length adjustable type.

Order **Part Number** — **Year**
DYYX6 — 15
DNX10

Days to Ship **Quotation**

Price **Quotation**

Character Designation Type

Indication	Part Number		Engraving characters (2 characters · Characters printed in blue in indications)	U/Price 1~9																					
	Type	No.																							
2 Characters	DYMx	4	<table border="1"> <tr><td>Name</td><td>Characters for engraving</td><td>Order code</td></tr> <tr><td>Slash</td><td>/</td><td>¥</td></tr> <tr><td>Greater</td><td>></td><td>></td></tr> <tr><td>Less</td><td><</td><td><</td></tr> <tr><td>Plus</td><td>+</td><td>+</td></tr> <tr><td>Minus</td><td>-</td><td>#</td></tr> <tr><td>Space</td><td>□</td><td>%</td></tr> </table>	Name	Characters for engraving	Order code	Slash	/	¥	Greater	>	>	Less	<	<	Plus	+	+	Minus	-	#	Space	□	%	Quotation
		Name		Characters for engraving	Order code																				
		Slash		/	¥																				
		Greater		>	>																				
		Less		<	<																				
		Plus		+	+																				
Minus	-	#																							
Space	□	%																							
5																									
6																									
8																									
10																									
12																									
16																									

2 characters can be engraved on the inside arrow.

Use ¥ for indicating / (slash), # for - (minus), and % for □ (space).


The inside arrows are the same with those of overall length adjustable type.

Order **Part Number** — **Characters for engraving**
DYMx10 — AB

Days to Ship **Quotation**

Price **Quotation**

OUTSIDE RINGS FOR PL EXCHANGE TYPE



Non JIS material definition is listed on P.1351 - 1352

RoHS

Outside Ring

D	Dm6	Dh7	L	E	a	b
4	4 +0.012/-0.004	4 0/-0.012		2.8		
5	5 +0.012/+0.004	5 0/-0.012	8	2.85		1.2
6	6 +0.012/-0.004	6 0/-0.012		2.9	1.0	
8	8 +0.015/+0.006	8 0/-0.015	10	3.4		
10	10 +0.018/+0.007	10 0/-0.018	12	4.2		1.5
12	12 +0.018/+0.007	12 0/-0.018	14	4.4	1.2	
16	16 +0.021/+0.008	16 0/-0.021	16	5.0	1.4	1.8
20	20 +0.021/+0.008	20 0/-0.021	16	5.3	1.5	2.0

Outside rings on this page are adapted for combination with inside arrows of date marked pin sets on P.571 and products on P.573

SUS420
50~53HRC

Year Switching Type

Indication	Outside rings divisions	Part Number		Year	U/Price 1~9
		Type	D		
4 years type	12 uniform divisions	DTX-R	4	15 for 2015~2018	Quotation
			5	※Days to ship will be 5-days for the adjustment of production after November 2015.	
			6		
			8	16 for 2016~2019 (available from Sept.,2015)	
			10	※Days to ship will be 5-days for the adjustment of production after November 2016.	
			12		
16	17 for 2017~2020 (available from Sept.,2016)				
20	※Days to ship will be 5-days for the adjustment of production after November 2017.				
6 years type	12 uniform divisions	DTXS-R	4	15 for 2015~2020	Quotation
			5	※Days to ship will be 5-days for the adjustment of production after November 2015.	
			6		
			8	16 for 2016~2021 (available from Sept.,2015)	
			10	※Days to ship will be 5-days for the adjustment of production after November 2016.	
			12		
16	17 for 2017~2022 (available from Sept.,2016)				
20	※Days to ship will be 5-days for the adjustment of production after November 2017.				

Order **Part Number** — **Year**
(Year) DTX-R16 — 15
(Month) DTDX-R16

Days to Ship **Quotation**

Price **Quotation**

Character Designation Type

Indication							
1M (1 place)	2M (2 places)	3M (3 places)	4M (4 places)	5M (5 places)	6M (6 places)	10M (10 places)	12M (12 places)
Engraving position	Engraving position	Engraving position	Engraving position	Engraving position	Engraving position	Engraving position	Engraving position

Up to 3 characters can be designated at each engraving position. Up to 2 characters can be designated at each engraving position. Only 1 character can be designated at each engraving position.

Part Number	Engraving characters (1~3 characters · Characters printed in blue in indications)	U/Price 1~9								
		1M	2M	3M	4M	5M	6M	10M	12M	
DTX-R	1M	4								
	2M	5								
	3M	6								
	4M	8								
	5M*	10								
	6M*	12								
	10M*	16								
	12M									

Use ¥ for indicating / (slash), # for - (minus), and % for □ (space) * Not applicable to D4 and D5 of 5M, 6M and 10M.

Order **Part Number** — **Characters for engraving** — **Characters for engraving** — **Characters for engraving** — **Characters for engraving** — **Characters for engraving** — **Characters for engraving** — **Characters for engraving** — **Characters for engraving** — **Characters for engraving** — **Characters for engraving**

DTX-R 3M 6 — POM — PS — SAN — 40 — 50 — 60 — F

DTX-R 6M 16 — 10 — 20 — 30 — 40 — 50 — 60 — F

DTX-R 12M 16 — % — 1 — 2 — 3 — 4 — 5 — F

Days to Ship **Quotation**

Price **Quotation**

Dividing of outside rings

1M · 2M · 3M · 4M	12 uniform divisions
6M · 12M	
5M · 10M	10 uniform divisions

Date Marked Pins
Recycle Marked Pins
Pins with Gas Vent