


# INSIDE ARROWS FOR PLATE-SIDE EXCHANGE TYPE

—STANDARD · SHALLOW ARROW MARK TYPE—



**RoHS**

**Inside Arrow**

No.	dh7	B	L	K
3	1.4	2		3
4	1.9	2.8	8	
5	2.3	3.4		
6	2.8	4		4
8	4	5.6	10	
10	5	6.5	12	
16	10	12	14	6
20	12	14	16	

No.	Arrow mark depth (mm)	
	Standard	Shallow
3	0.22	—
4	0.25	0.14
5	0.30	0.16
6	0.40	0.18
8	0.40	0.20
10~20	0.50	0.22

SUS420  
 50~53HRC

**Details** P.570

Inside arrows on this page are adapted for combination with outside rings of date marked pin sets on **P.575 · 581**, and products on **P.578 · 582**.

Year Type				No-marking Type				
Indication	Part Number		Year	U/Price1~9	Indication	Part Number		U/Price1~9
	Type	No.				Type	No.	
Year	DYY DYYU (Shallow arrow) ⊕ Except for No.3	3	15 for 2015	Quotation	No-marking	DN DNU (Shallow arrow) ⊕ Except for No.3	3	Quotation
		4	※Days to ship will be 5-days for the adjustment of production after November 2015.				4	
		5					5	
		6	16 for 2016 (available from Sept.,2015)				6	
		8	※Days to ship will be 5-days for the adjustment of production after November 2016.				8	
		10					10	
16	17 for 2017 (available from Sept.,2016)	16						
20	※Days to ship will be 5-days for the adjustment of production after November 2017.	20						

Order: Part Number (Year) **DYY6** — Year **15**  
 (No-marking) **DN10**

Days to Ship: **Quotation**

Price: **Quotation**

**Character Designation Type**

Indication	Part Number		Engraving characters (2 characters · Characters printed in blue in indications)	U/Price 1~9
	Type	No.		
2 characters	DYM	5	0 1 2 3 4 5 6 7 8 9 A B C D E J F G H I O T K L M N S Y P Q R V X U Z	Quotation
		6		
		8		
		10		
		16		
		20		

Name	Characters for engraving	Order code
Slash	/	¥
Greater	>	>
Less	<	<
Plus	+	+
Minus	-	#
Space	□	%


2 characters can be engraved on the inside arrow.  
 Use ¥ for indicating / (slash), # for — (minus), and % for □ (space).

Order: Part Number **DYM10** — Characters for engraving **AB**

Days to Ship: **Quotation**

Price: **Quotation**

# OUTSIDE RINGS FOR PLATE-SIDE EXCHANGE TYPE



**RoHS**

**Outside Ring**

Dm6	Dh7	dh7	L
3	3	1.4	8
4	4	1.9	8
5	5	2.3	8
6	6	2.8	8
8	8	4	10
10	10	5	12
16	16	10	14
20	20	12	16

SUS420  
 50~53HRC

**Details** P.570

Outside rings on this page are adapted for combination with inside arrows of date marked pin sets on **P.575**, and products on **P.577**.

Year Switching Type				Month · Day · No-marking Type						
Indication	Outside rings divisions	Part Number		Year	U/Price 1~9	Indication	Outside rings divisions	Part Number		U/Price 1~9
		Type	D					Type	D	
4 years type	12 uniform divisions	DT-R	4	15 for 2015~2018	Quotation	Month	12 uniform divisions	DTC-R	3	Quotation
			5	※Days to ship will be 5-days for the adjustment of production after November 2015.					4	
			6						5	
			8	16 for 2016~2019 (available from Sept.,2015)					6	
			10	※Days to ship will be 5-days for the adjustment of production after November 2016.					8	
			16	17 for 2017~2020 (available from Sept.,2016)					10	
20	※Days to ship will be 5-days for the adjustment of production after November 2017.	16								
6 years type	12 uniform divisions	DTS-R	4	15 for 2015~2020	Quotation	Day (1st digit)	10 uniform divisions	DTE-R	4	Quotation
			5	※Days to ship will be 5-days for the adjustment of production after November 2015.					5	
			6						6	
			8	16 for 2016~2021 (available from Sept.,2015)					8	
			10	※Days to ship will be 5-days for the adjustment of production after November 2016.					10	
			16	17 for 2017~2022 (available from Sept.,2016)					16	
20	※Days to ship will be 5-days for the adjustment of production after November 2017.	20								
Day (2nd digit)	12 uniform divisions	DTF-R	4		Quotation	Day	31 uniform divisions	DTG-R	4	Quotation
			5						5	
			6						6	
			8						8	
			10						10	
			16						16	
20		20								
No-marking	12 uniform divisions	DTN-R	4		Quotation	No-marking	12 uniform divisions	DTN-R	4	Quotation
			5						5	
			6						6	
			8						8	
			10						10	
			16						16	
20		20								

Order: Part Number (Year) **DT-R16** — Year **15**  
 (Month) **DTD-R10**

Days to Ship: **Quotation**

Price: **Quotation**

**Character Designation Type**

Indication							
1M (1 place)	2M (2 places)	3M (3 places)	4M (4 places)	5M (5 places)	6M (6 places)	10M (10 places)	12M (12 places)
Engraving position	Engraving position	Engraving position	Engraving position	Engraving position	Engraving position	Engraving position	Engraving position

Outside ring is divided equally among ten.  
 Outside rings is divided equally among ten.

Up to 3 characters can be designated at each engraving position. Up to 2 characters can be designated at each engraving position. Only 1 character can be designated at each engraving position.

Type	Part Number		Engraving characters (1~3 characters · Characters printed in blue in indications)	U/Price 1~9
	Indication	D		
DT-R	1M	5	0 1 2 3 4 5 6 7 8 9 A B C D E J F G H I O T K L M N S Y P Q R V X U Z	Quotation
	2M	6		
	3M	8		
	4M	10		
	5M	16		
	6M	20		
	10M			
	12M			

Not applicable to D5 of DT-R5M and DT-R6M. Use ¥ for indicating / (slash), # for — (minus), and % for □ (space).

Order: Part Number **DT-R 3M 6- POM** — **PS** — **SAN**  
**DT-R 6M 20- JP** — **US** — **CN** — **KR** — **TH** — **TW**  
**DT-R12M 16- %** — **1** — **2** — **3** — **4** — **5** — **F**

Days to Ship: **Quotation**

Price: **Quotation**

Dividing of outside rings:  
 1M · 2M · 3M · 4M 12 uniform divisions  
 6M · 12M  
 5M · 10M 10 uniform divisions

Date Marked Pins  
 Recycle Marked Pins  
 Pins with Gas Vent