

STROKE END BLOCKS

STROKE END BLOCKS / END BLOCK CHAINS

— SQUARE HARDENED TYPE —

RoHS

Catalog No.	Components
SBS	① ② ③ ④ ⑤
SBN	① ② ③ ④ ⑤
SEC	① ② ③ ④ ⑤

① ② M S45C
③ SCM435
Strength class 12.9
JIS B 0205 Grade 2
④ Chain
⑤ C-ring JIS B 2804

SEC

Catalog No.	②	①	Base unit price 1 ~ 9 pieces		
Type	D	L	T	Color	Color
		0.1mm increments	5mm increments		
SBS ①②③④⑤	14				
	16	22.0 ~ 100.0			
	18				
	20	22.0 ~ 120.0			
	25	22.0 ~ 170.0			
	32				
	38				
SBN ②③	50	25.0 ~ 200.0			
	60				

③ Bolt size table									
D	d	d ₁	M×P	ℓ	ℓ ₁	L	③		
14	7	8	M4	10	10	22.0 ~ 80.0	M4×20		
16	8	8	M4	10	10	22.0 ~ 80.0	M4×20		
18	8.5	9.5	M5	10	10	22.0 ~ 80.0	M5×20		
20	10	11	M6	11	11	22.0 ~ 80.0	M6×20		
25	13	14	M8	12	12	22.0 ~ 80.0	M8×20		
32	14	14	M8	12	12	22.0 ~ 80.0	M8×20		
38	16	17	M10	16	16	25.0 ~ 80.0	M10×25		
50	18	20	M12	18	18	25.0 ~ 80.0	M12×25		
60	18	20	M12	18	18	25.0 ~ 80.0	M12×25		

Catalog No.	①	Base unit price
Type	D	1 ~ 9 pieces
SEC ①④⑤	14	
	16	
	18	
	20	10 ~ 50
	25	
	32	
	38	
SBN ②③	50	10 ~ 50
	60	55 ~ 100

● N (Normal) → S Black oxide (Fe₃O₄)
● Select colors for the body and spacer cap as needed in order to prevent incidents of forgetting to remove the spacer cap.
Note: Be sure to specify the color of the spacer cap even when the colors of the body and spacer cap are the same.
● When used in cases such as (B), if the SBS body is 30 mm or less, the bolt head and spacer cap may interfere. Be sure that the spacer cap faces upward when it is used.

Order

Days to Ship

Price

Quotation

Quotation

Quotation

Example

Alterations

SEC

Alteration	Code	Spec.	1Code
LKC		L dimension tolerance change L +0.1 → ±0.01 ● When LKC is used, L dimension can be selected in 0.01mm increments. ● Resulting in variation of the finished L dimension of 0.005 or less. ● Can be used for SBS and SBN.	
CHC		Change to standard chain length. L (CHC Selection) 22.0 ~ 49.9 50 100 200 50.0 ~ 99.9 100 200 100.0 ~ 200.0 200	
RS		Change from the standard chain to a reinforced chain. ● Can be used for SBS20 ~ 60 and SEC20 ~ 60. ● Can be used for SBS and SEC when T ≥ 20. ● Length is 200 only.	
NMC		Addition of a groove for height adjustment ● Can be used for SBS SBN with D32 or larger.	

Stroke end blocks

SBVK

① SKS93
② SCM435
Strength class 12.9
(JIS B 0205 Grade 2)

M×P	ℓ	d ₁	d ₂	h	Catalog No.		B	①		②		Base unit price 1 ~ 9 pieces		
					Type	A		L 0.1mm increments	Color	L1 5mm increments	L2.0 ~ 40.0	L4.0 ~ 70.0	L7.0 ~ 100.0	
M4×0.7	8 12	8	5	13	SBVK	13	32 50	20.0 ~ 50.0	R (Red) Y (Yellow) N (Normal)	15 ~ 50				
M5×0.8	10 14	9.5	6			16	38 65	20.0 ~ 80.0		15 ~ 80	Quotation			
M6×1.0	12 16	11	7			19	50 75	20.0 ~ 100.0		15 ~ 100				

Order

Price

Alterations

Quotation

Quotation

Quotation

End Block Chains

RSC

① SWM-B
Bright chromate plating
② SPCC
③ SS400 (Lifting eye bolt M10×20) with nut

Order

Days to Ship

Price

Example

Quotation

Quotation

Quotation

COMPONENTS