

Cuscinetti con supporto
Con pilota e anello di sicurezza

Technical drawings and specifications for bearings with support. Includes images of different bearing types (Rotondi, Quadrati, Compatti) and detailed cross-sectional views with dimensions (d, D, B, H, W, T, T1, S, l1, dh, D197, P.C.D., K, A, F, M, d1, H1). A table lists the material (Materiale), surface treatment (Trattamento superficie), and safety ring (Anello di sicurezza) for various bearing types and sizes. A note indicates that bearings with rubber seals (VV and DD) are made of steel.

Codice componente		Guarnizione	d	DH7	Tolleranza	B	H	W	T	T1	S	l1	dh	D197	Tolleranza	P.C.D.	K	A	F	M (fil. grossa)(d2)	d1	H1
Tipo	N. cuscinetto																					
(Rotondi)	BGRRB	ZZ Doppia schermatura	3	10	+0.015	4	33	16	9	7	2	2	7	14	-0.006 -0.024	24	27	24	-	M4 (3.3)	6.5	3.4
	BGRR		4	13	+0.018 0	5	35	18	10	8			9	17		26	28	26				
	BARR		5	14		5	36	20	10	8			10	18		26	30	26				
	SBARR		6	16		5	38	22	10	8			12	20		28	31	28				
	SBGRR		6	17		6	39	23	11	9			13	21		29	32	29				
	BGSRB		6	19		6	41	25	11	9			15	24		31	34	31				
	BGSR		8	22		7	45	29	12	10			15	24		31	34	31				
	BACR		8	24		8	47	32	13	11			18	27		35	36	35				
	SBACR		24	29		8	47	32	13	11			20	30		37	37	37				
	SBGCR		24	30		5	41	25	10	8			15	24		31	34	31				
(Quadrati)	BGRRB	ZZ Doppia schermatura	10	22	+0.021 0	6	45	29	11	9	2	2	19	27	-0.007 -0.028	35	36	35	-	M5 (4.3)	8	4.4
	BGRR		10	26		8	50	34	13	11			22	32		40	39	40				
	BARR		10	30		9	54	38	14	12			24	36		44	42	44				
	SBARR		12	21		5	44	29	10	8			17	26		34	35	34				
	SBGRR		12	24		6	48	31	11	9			21	30		38	38	38				
	BGSRB		12	28		8	52	36	13	11			24	34		42	40	42				
	BGSR		15	32		10	56	40	15	13			26	38		46	43	46				
	BACR		15	35		5	47	32	10	8			20	30		37	37	37				
	SBACR		15	32		9	60	40	14	12			28	38		48	46	48				
	SBGCR		15	35		11	64	44	17	15			29	42		52	49	52				
(Compatti)	BGRRB	ZZ Doppia schermatura	17	30	+0.021 0	7	60	38	12	10	3	3	27	36	-0.009 -0.034	48	46	48	-	M6 (5.2)	9.5	5.4
	BGRR		17	35		10	66	44	16	14			31	42		54	50	54				
	BARR		17	40		12	72	50	18	16			34	48		60	54	60				
	SBARR		20	37		7	60	40	12	10			28	38		48	46	48				
	SBGRR		20	42		9	69	47	15	13			34	45		56	54	51				
	BGSRB		20	47		12	77	54	18	16			36	50		64	59	56				
	BGSR		25	42		14	81	58	20	18			40	54		68	62	59				
	BACR		25	47		7	69	47	13	11			34	45		56	54	51				
	SBACR		25	52		9	77	54	15	13			36	50		64	59	56				
	SBGCR		25	57		12	88	58	18	16			41	54		72	67	63				
	BGRRB	ZZ Doppia schermatura	30	42	+0.030 0	15	94	64	22	20	3	3	45	60	-0.010 -0.040	78	72	68	-	M10 (8.5)	14	8.6
	BGRR		30	47		7	77	54	13	11			36	50		64	59	56				
	BARR		30	52		9	88	58	15	13			41	54		72	67	63				
	SBARR		30	55		13	96	66	20	18			48	62		80	73	70				
	SBGRR		30	62		16	104	74	23	21			55	70		88	79	77				
	BGSRB		35	72		17	126	88	26	23			64	84		105	95	92				
	BGSR		35	68		15	114	82	23	21			60	78		96	86	80				
	BACR		40	80		18	134	96	27	24			74	92		113	102	98				
	SBACR		40	86		25	154	110	31	28			83	106		126	115	110				
	SBGCR		50	90		20	147	110	31	28			83	106		126	115	110				

*1 N. 623, 624, 605 e 606 non disponibili per VV (tenuta non strisciante).
*2 I cuscinetti con tenute in gomma sono tutti in acciaio.

Ordering Example: BGRR 6000 ZZ. Includes a table for component codes (Tipo, Cuscinetto, Guarnizione) and a note about the safety ring (Anello di sicurezza).

N. cusci- netto	Guarni- zione	Prezzo unitario															
		Rotondi					Quadrati					Compatti					
		BGRRB	BGRR	BARR	SBARR	SBGRR	BGSRB	BGSR	BASR	SBASR	SBGSR	BGCRB	BGCR	BACR	SBACR	SBGCR	
623	ZZ (x1.0)				-	-				-	-				-	-	
624					-	-				-	-				-	-	
605					-	-				-	-				-	-	
625					-	-				-	-				-	-	
606																	
626																	
698																	
608																	
628																	
6800																	
6900																	
6000																	
6200																	
6801																	
6901																	
6001																	
6201																	
6802																	
6902																	
6002																	
6202	VV (x1.1)																
6903																	
6003																	
6203																	
6804																	
6904																	
6004																	
6204																	
6805				-	-	-			-	-	-			-	-	-	
6905				-	-	-			-	-	-			-	-	-	
6005			-	-	-			-	-	-			-	-	-		
6205			-	-	-			-	-	-			-	-	-		
6806			-	-	-			-	-	-			-	-	-		
6906			-	-	-			-	-	-			-	-	-		
6006			-	-	-			-	-	-			-	-	-		
6206			-	-	-			-	-	-			-	-	-		
6007			-	-	-			-	-	-			-	-	-		
6207			-	-	-			-	-	-			-	-	-		
6008			-	-	-			-	-	-			-	-	-		
6208			-	-	-			-	-	-			-	-	-		
6010			-	-	-		-	-	-	-			-	-	-		
6210			-	-	-		-	-	-	-			-	-	-		