


Cuscinetti con supporto

Anello esterno incorporato, con pilota

Cuscinetti con supporto

Anello esterno incorporato, a T



Precisione cuscinetto: JIS B 1514 Classe 0

Codice componente		Selezione L	S	d	DH7	Tolleranza	B	b1	H	D2	T	dh	D196	Tolleranza	P.C.D.	d1	d2	H1	T1
Tipo	N. cuscinetto																		
GBGYB (Ossido nero)	6902ZZ	40 60 80	10	15	28	+0.021 0	7	9	70	43	12	25	45	-0.009 -0.025	62	11	6.6	6.5	6
	6002ZZ	50 70 90			32	+0.025 0	9	11	75	48		28	50						
	6903ZZ	50 70 90		17	30	+0.021 0	7	9	70	43		27	45						
	6003ZZ	60 80 100			35		10	12	75	48		31	50						
GBGY (Nichelatura chimica)	6904ZZ	60 80 100	15	20	37	+0.025 0	9	11	87	53	15	34	55	-0.010 -0.029	75	14	9	8.5	7
	6004ZZ	70 100			42		12	14	92	58		36	60						
	6005ZZ	70 100		25	47		13	15	98	63		41	65						8
	6006ZZ	70 100			55		14	16	120	78		48	80						
	6007ZZ	80 100		35	62	+0.030 0	14	16	126	84		55	86	-0.012 -0.034	106	17.5	11	10.5	9
	6008ZZ	80 100			68		15	17	140	92		60	95						


Ordering Example

Codice componente	-	L
Tipo	Cuscinetto	
GBGYB	6005ZZ	- 70

N. cuscinetto	L	GBGYB		GBGY	
		Prezzo unitario	Sconto volumi elevati	Prezzo unitario	Sconto volumi elevati
		1 pz.	2-4 pz.	1 pz.	2-4 pz.
6902ZZ	40				
	60				
	80				
6002ZZ	50				
	70				
	90				
6903ZZ	50				
	70				
	90				
6003ZZ	60				
	80				
	100				
6904ZZ	60				
	80				
	100				

N. cuscinetto	L	GBGYB		GBGY	
		Prezzo unitario	Sconto volumi elevati	Prezzo unitario	Sconto volumi elevati
		1 pz.	2-4 pz.	1 pz.	2-4 pz.
6004ZZ	70				
	100				
6005ZZ	70				
6006ZZ	70				
	100				
6007ZZ	80				
	100				
6008ZZ	80				
	100				

Per ordini superiori ai valori indicati, richiedere un preventivo.



Precisione cuscinetto: JIS B 1514 Classe 0

Codice componente		Larghezza T selezionabile	Altezza h selezionabile	d	DH7	Tolleranza	B	b1	H	dh	L	L1	L2	S	G	W	d1	T1
Tipo	N. cuscinetto																	
GBGWB (Ossido nero)	6902ZZ	30 50	30 40 50	15	28	+0.021 0	7	9	h+18	25	60	48	36	12	7.5	34	6.6	6
	6002ZZ	40 60	30 40 50		32	+0.025 0	9	11	h+20	28	64	52	40					
	6903ZZ	40 60	30 40 50	17	30	+0.021 0	7	9	h+19	27	62	50	38					
	6003ZZ	40 60	30 40 50		35		10	12	h+22	31	68	56	44					
GBGW (Nichelatura chimica)	6904ZZ	40 60	40 50 60	20	37	+0.025 0	9	11	h+23	34	76	61	46	15	10	44	9	7
	6004ZZ	50 80	40 50 60		42		12	14	h+25	36	80	65	50					
	6005ZZ	50 80	50 60	25	47		13	15	h+28	41	86	71	56					
	6006ZZ	50 80	50 60		55	+0.030 0	13	15	h+32	48	104	84	64					

Ordering Example

Codice componente	-	T	-	h
Tipo	Cuscinetto			
GBGWB	6903ZZ	- 40	- 40	

N. cuscinetto	T	GBGWB		GBGW	
		Prezzo unitario	Sconto volumi elevati	Prezzo unitario	Sconto volumi elevati
		1 pz.	2 ~ 4 pz.	1 pz.	2 ~ 4 pz.
6902ZZ	30				
	50				
6002ZZ	40				
	60				
6903ZZ	40				
	60				
6003ZZ	40				
	60				
6904ZZ	40				
	60				
6004ZZ	50				
	80				
6005ZZ	50				
	80				
6006ZZ	50				
	80				

Per ordini superiori ai valori indicati, richiedere un preventivo.