





Maniglie a ripresa con pulsante in plastica/Maniglie a ripresa di sicurezza in plastica

Maniglie a ripresa a cricchetto/Leve rapide





Codice componente		Selezione L										Carico max Fmax (N)			Forza serraggio max Pmax (kN)			Massa di riferimento (g)			Prezzo unitario							
Tipo	M																											
Filettate CLNPP CLSPP	4	20										21	1.7		18													
	5	12	16	20	25	32						42	2.7															
	6	12	16	20	25	32	40						70	3.8		20												
	8	16	20	25	32	40	50	65	44.5	46.5	40.5	3.5	18	14	20	1.3	120	7		40								
	10	20	25	32	40	50						82	54	56	47	6.5	21	16	24	1.3	200	11		80				
	12	25	40						92	64	66	56	6.5	25	19	28	1.3	290	16		120							




Codice componente		Selezione L						Numero di dentelli	Carico max Fmax (N)	Forza serraggio max Pmax (kN)	Massa di riferimento (g)	Prezzo unitario
Tipo	M											
Filettate CLNPA	4	12	20					16	21	1.7	18	
	5	12	16	20	25	32	42		2.7			
	6	12	16	20	25	32	70		3.8			

Ordering Example: CLNPA - 20 - 12



Codice componente		Selezione L					Colore leva	R	H	h	D	d	Carico max Fmax (N)	Forza serraggio max Pmax (kN)	Massa di riferimento (g)	Prezzo unitario
Tipo	M															
CLRA	5	16	25				B (Nero)	55	35	26	17	10	108	4.8	61	
	6	20	32					68	45	33	18	14	184	6.8	63	
	8	25	40										316	12.5	101	
	10	32	50										507	19.8	112	

Ordering Example: CLRA 5 - 25 - B



Codice componente		Selezione L				Colore leva	(st)	D	d	T	S	Massa di riferimento (g)	Prezzo unitario	Forza di serraggio (N)	Carico leva (N)
Tipo	M														
CLCK	5	30	40			B (Nero)	2.6	16	14	12	4	122	1000	18	
	6	40	50				2.6	19	16	14	4	136	2000	36	
	8	50	60				2.6	24	20	17	5	170	3000	78	

Ordering Example: CLCK 6 - 40 - B

Example: Leve rapide

