


Molle a spirale


Carico leggero SWL



RoHS10

Molle a spirale

Carico medio SWM



RoHS10

D	d	L	Costante molla		F=Lx32% Fmm	F=Lx36% Fmm	F=Lx40% Fmm	Codice componente D-L	Prezzo unitario
			N/mm(kgf/mm)	N(kgf)					
6	3	15	13.1(1.33)	4.8	5.4	6.0	SWL 6-	15	
		20	9.8(1.00)	6.4	7.2	8.0			
		25	7.8(0.80)	8.0	9.0	10.0			
		30	6.5(0.67)	9.6	10.8	12.0			
		35	5.6(0.57)	11.2	12.6	14.0			
		40	4.9(0.50)	12.8	14.4	16.0			
8	4	10	24.5(2.50)	3.2	3.6	4.0	SWL 8-	10	
		15	16.3(1.67)	4.8	5.4	6.0			
		20	12.3(1.25)	6.4	7.2	8.0			
		25	9.8(1.00)	8.0	9.0	10.0			
		30	8.2(0.83)	9.6	10.8	12.0			
		35	7.0(0.71)	11.2	12.6	14.0			
		40	6.1(0.63)	12.8	14.4	16.0			
		45	5.4(0.56)	14.4	16.2	18.0			
		50	4.9(0.50)	16.0	18.0	20.0			
		55	4.5(0.45)	17.6	19.8	22.0			
		60	4.1(0.42)	19.2	21.6	24.0			
		65	3.8(0.38)	20.8	23.4	26.0			
70	3.5(0.36)	22.4	25.2	28.0					
75	3.3(0.33)	24.0	27.0	30.0					
80	3.1(0.31)	25.6	28.8	32.0					
10	5	10	34.3(3.50)	3.2	3.6	4.0	SWL 10-	10	
		15	22.9(2.33)	4.8	5.4	6.0			
		20	17.2(1.75)	6.4	7.2	8.0			
		25	13.7(1.40)	8.0	9.0	10.0			
		30	11.4(1.17)	9.6	10.8	12.0			
		35	9.8(1.00)	11.2	12.6	14.0			
		40	8.6(0.88)	12.8	14.4	16.0			
		45	7.6(0.78)	14.4	16.2	18.0			
		50	6.9(0.70)	16.0	18.0	20.0			
		55	6.2(0.64)	17.6	19.8	22.0			
		60	5.7(0.58)	19.2	21.6	24.0			
		65	5.3(0.54)	20.8	23.4	26.0			
70	4.9(0.50)	22.4	25.2	28.0					
75	4.6(0.47)	24.0	27.0	30.0					
80	4.3(0.44)	25.6	28.8	32.0					
90	3.8(0.39)	28.8	32.4	36.0					
12	6	15	34.3(3.50)	4.8	5.4	6.0	SWL 12-	15	
		20	25.7(2.63)	6.4	7.2	8.0			
		25	20.6(2.10)	8.0	9.0	10.0			
		30	17.2(1.75)	9.6	10.8	12.0			
		35	14.7(1.50)	11.2	12.6	14.0			
		40	12.9(1.31)	12.8	14.4	16.0			
		45	11.4(1.17)	14.4	16.2	18.0			
		50	10.3(1.05)	16.0	18.0	20.0			
		55	9.4(0.95)	17.6	19.8	22.0			
		60	8.6(0.88)	19.2	21.6	24.0			
		65	7.9(0.81)	20.8	23.4	26.0			
		70	7.4(0.75)	22.4	25.2	28.0			
75	6.9(0.70)	24.0	27.0	30.0					
80	6.4(0.66)	25.6	28.8	32.0					
90	5.7(0.58)	28.8	32.4	36.0					
14	7	20	34.3(3.50)	6.4	7.2	8.0	SWL 14-	20	
		25	27.5(2.80)	8.0	9.0	10.0			
		30	22.9(2.33)	9.6	10.8	12.0			
		35	19.6(2.00)	11.2	12.6	14.0			
		40	17.2(1.75)	12.8	14.4	16.0			
		45	15.3(1.56)	14.4	16.2	18.0			
		50	13.7(1.40)	16.0	18.0	20.0			
		55	12.5(1.27)	17.6	19.8	22.0			
		60	11.4(1.17)	19.2	21.6	24.0			
		65	10.6(1.08)	20.8	23.4	26.0			
		70	9.8(1.00)	22.4	25.2	28.0			
		75	9.2(0.93)	24.0	27.0	30.0			
80	8.6(0.88)	25.6	28.8	32.0					
90	7.6(0.78)	28.8	32.4	36.0					
100	6.9(0.70)	32.0	36.0	40.0					

D	d	L	Costante molla		F=Lx32% Fmm	F=Lx36% Fmm	F=Lx40% Fmm	Codice componente D-L	Prezzo unitario
			N/mm(kgf/mm)	N(kgf)					
16	8	20	42.9(4.38)	6.4	7.2	8.0	SWL 16-	20	
		25	34.3(3.50)	8.0	9.0	10.0			
		30	28.6(2.92)	9.6	10.8	12.0			
		35	24.5(2.50)	11.2	12.6	14.0			
		40	21.5(2.19)	12.8	14.4	16.0			
		45	19.1(1.94)	14.4	16.2	18.0			
		50	17.2(1.75)	16.0	18.0	20.0			
		55	15.6(1.59)	17.6	19.8	22.0			
		60	14.3(1.46)	19.2	21.6	24.0			
		65	13.2(1.35)	20.8	23.4	26.0			
		70	12.3(1.25)	22.4	25.2	28.0			
		75	11.4(1.17)	24.0	27.0	30.0			
80	10.7(1.09)	25.6	28.8	32.0					
90	9.5(0.97)	28.8	32.4	36.0					
100	8.6(0.88)	32.0	36.0	40.0					
125	6.9(0.70)	40.0	45.0	50.0					
18	9	20	52.7(5.38)	6.4	7.2	8.0	SWL 18-	20	
		25	42.4(4.30)	8.0	9.0	10.0			
		30	35.1(3.58)	9.6	10.8	12.0			
		35	30.1(3.07)	11.2	12.6	14.0			
		40	26.4(2.69)	12.8	14.4	16.0			
		45	23.4(2.39)	14.4	16.2	18.0			
		50	21.1(2.15)	16.0	18.0	20.0			
		55	19.2(1.95)	17.6	19.8	22.0			
		60	17.6(1.79)	19.2	21.6	24.0			
		65	16.2(1.65)	20.8	23.4	26.0			
		70	15.1(1.54)	22.4	25.2	28.0			
		75	14.1(1.43)	24.0	27.0	30.0			
80	13.2(1.34)	25.6	28.8	32.0					
90	11.7(1.19)	28.8	32.4	36.0					
100	10.5(1.08)	32.0	36.0	40.0					
125	8.4(0.86)	40.0	45.0	50.0					
20	10	20	66.2(6.75)	6.4	7.2	8.0	SWL 20-	20	
		25	53.0(5.40)	8.0	9.0	10.0			
		30	44.1(4.50)	9.6	10.8	12.0			
		35	37.8(3.86)	11.2	12.6	14.0			
		40	33.1(3.38)	12.8	14.4	16.0			
		45	29.4(3.00)	14.4	16.2	18.0			
		50	26.5(2.70)	16.0	18.0	20.0			
		55	24.1(2.45)	17.6	19.8	22.0			
		60	22.1(2.25)	19.2	21.6	24.0			
		65	20.4(2.08)	20.8	23.4	26.0			
		70	18.9(1.93)	22.4	25.2	28.0			
		75	17.7(1.80)	24.0	27.0	30.0			
80	16.5(1.69)	25.6	28.8	32.0					
90	14.7(1.50)	28.8	32.4	36.0					
100	13.2(1.35)	32.0	36.0	40.0					
125	10.6(1.08)	40.0	45.0	50.0					
150	8.8(0.90)	48.0	54.0	60.0					
22	11	25	65.7(6.70)	8.0	9.0	10.0	SWL 22-	25	
		30	54.8(5.58)	9.6	10.8	12.0			
		35	46.9(4.79)	11.2	12.6	14.0			
		40	41.1(4.19)	12.8	14.4	16.0			
		45	36.5(3.72)	14.4	16.2	18.0			
		50	32.9(3.35)	16.0	18.0	20.0			
		55	29.9(3.05)	17.6	19.8	22.0			
		60	27.4(2.79)	19.2	21.6	24.0			
		65	25.3(2.58)	20.8	23.4	26.0			
		70	23.5(2.39)	22.4	25.2	28.0			
		75	21.9(2.23)	24.0	27.0	30.0			
		80	20.5(2.09)	25.6	28.8	32.0			
90	18.3(1.86)	28.8	32.4	36.0					
100	16.4(1.68)	32.0	36.0	40.0					
125	13.1(1.34)	40.0	45.0	50.0					
150	11.0(1.12)	48.0	54.0	60.0					
25	12.5	25	82.4(8.40)	8.0	9.0	10.0	SWL 25-	25	
		30	68.7(7.00)	9.6	10.8	12.0			
		35	58.8(6.00)	11.2	12.6	14.0			
		40	51.5(5.25)	12.8	14.4	16.0			
		45	45.8(4.67)	14.4	16.2	18.0			
		50	41.2(4.20)	16.0	18.0	20.0			
		55	37.4(3.82)	17.6	19.8	22.0			
		60	34.3(3.50)	19.2	21.6	24.0			
		65	31.7(3.23)	20.8	23.4	26.0			
		70	29.4(3.00)	22.4	25.2	28.0			
		75	27.5(2.80)	24.0	27.0	30.0			
		80	25.7(2.63)	25.6	28.8	32.0			
90	22.9(2.33)	28.8	32.4	36.0					
100	20.6(2.10)	32.0	36.0	40.0					
125	16.5(1.68)	40.0	45.0	50.0					
150	13.7(1.40)	48.0	54.0	60.0					
175	11.8(1.20)	56.0	63.0	70.0					
200	10.3(1.05)	64.0	72.0	80.0					

D	d	L	Costante molla		F=Lx25.6% Fmm	F=Lx28.8% Fmm	F=Lx32% Fmm	Codice componente D-L	Prezzo unitario			
			N/mm(kgf/mm)	N(kgf)								
6	3	15	20.4(2.08)	3.8	4.3	4.8	SWL 6-	15				
		20	15.3(1.56)	5.1	5.8	6.4						
		25	12.3(1.25)	6.4	7.2	8.0						
		30	10.2(1.04)	7.7	8.6	9.6						
		35	8.8(0.89)	9.0	10.1	11.2						
		40	7.7(0.78)	10.2	11.5	12.8						
		45	6.8(0.69)	11.5	13.0	14.4						
		50	6.1(0.63)	12.8	14.4	16.0						
		55	5.6(0.57)	14.1	15.8	17.6						
		60	5.1(0.52)	15.4	17.3	19.2						
		8	4	10	42.9(4.37)	2.6			2.9	3.2	SWL 8-	10
				15	28.6(2.91)	3.8			4.3	4.8		
20	21.5(2.18)			5.1	5.8	6.4						
25	17.2(1.75)			6.4	7.2	8.0						
30	14.3(1.46)			7.7	8.6	9.6						
35	12.2(1.25)			9.0	10.1	11.2						
40	10.7(1.09)			10.2	11.5	12.8						
45	9.5(0.97)			11.5	13.0	14.4						
50	8.6(0.87)			12.8	14.4	16.0						
55	7.8(0.79)			14.1	15.8	17.6						
60	7.1(0.73)			15.4	17.3	19.2						
65	6.6(0.67)			16.6	18.7	20.8						
70	6.1(0.62)	17.9	20.2	22.4								
75	5.7(0.58)	19.2	21.6	24.0								
80	5.4(0.55)	20.5	23.0	25.6								
10	5	10	61.3(6.25)	2.6	2.9	3.2	SWL 10-	10				
		15	40.9(4.17)	3.8	4.3	4.8						
		20	30.6(3.13)	5.1	5.8	6.4						
		25	24.5(2.50)	6.4	7.2	8.0						
		30	20.4(2.08)	7.7	8.6	9.6						
		35	17.5									