

ADJUSTMENT PINS

RoHS

M	Characters	Catalog No.	S
SKS3	With characters	PIN	Black oxide
58 ~ 60HRC	No characters	PIN-N	(Fe ₃ O ₄)
Equivalent to SKD11	With characters	PINH	No surface
58 ~ 60HRC	No characters	PINH-N	treatment

Catalog No.	L	(PIN·PINH only)
Type	0.1mm increments	CHR (characters)
(With characters) PIN	3	
	4	
	5	
	6	
	7	
	8	
(No characters) PIN-N	9	
	10	
	11	
	12	
High-hardness type	13	
	14	
(With characters) PINH	15	
	16	
	18	
(No characters) PINH-N	20	
	22	
	25	
	27	
	30	

10.0 ~ 250.0

EX Example

Identifying markings can be created on the side.

Character type	Number of characters
- Alphabet letters	1 ~ 8 characters
- Numbers	(If L < 30.0, then the number of characters is 1 ~ 3.)

Ⓜ The character font is Gothic.
Ⓧ — (hyphen) and / (slash) cannot be selected.

Order Catalog No. — L — CHR
PIN 10 — 60.5 — 53218A
PINH-N8 — 156.2

Days to Ship **Quotation**

Price **Quotation**

Alterations Catalog No. — L — CHR — (LKC-NC)
PINH 8 — 105.5 — A10 — LKC
PINH-N 20 — 125.5 — — NC

Alteration	Code	Spec.	1Code
	LKC	Full length tolerance change L ± 0.1 ⇨ +0.05 / 0	Quotation
	NC	No chamfering of either end	Quotation

PRESSURE PINS

RoHS

PRPS (Fall-out prevention type)

PRP

SKS3 58 ~ 60 HRC

SWPA Included for PRPS only.

Catalog No.	L	PRPS Base unit price 1~9 pieces	PRP Base unit price 1~9 pieces
Type	D	L40.0 ~ 100.0	L20.0 ~ 150.0
PRPS (L ≥ 40)	8	~ 100.0	~ 150.0
	10	~ 150.0	~ 200.0
	13	~ 200.0	~ 250.0
PRP	16	~ 100.0	~ 150.0
	20	~ 150.0	~ 200.0
	25	~ 200.0	~ 250.0
	28	~ 250.0	~ 300.0

Quotation

Alterations Catalog No. — L — (LKC)
PRPS 20 — 130 — LKC

Alteration	Code	Spec.	1Code
	LKC	Full length tolerance change +0.3 ⇨ L20.0 ~ 100.0: +0.03 / 0 +0.1 ⇨ L100.1 ~ 150.0: +0.04 / 0 L150.1 ~ 200.0: +0.05 / 0	Quotation

Ⓜ When LKC is used, L dimension can be selected in 0.1mm increments.

Fall-out prevention stopper

PRPS-K **RoHS**

Catalog No.	Base unit price	Volume discount unit price
PRPS-K	1 ~ 9 pieces	10 ~ 19 / 20 ~ 49 / 50 ~ 100
		Quotation

Order Catalog No. **PRPS-K**

Days to Ship **Quotation**

SWPA

Collars for pressure pins

PRPCC **RoHS**

D	Catalog No.	Base unit price
Type	d	1 ~ 9 pieces
11	8	
13	10	
16	13	
19	16	
24	20	
29	25	
32	28	

Quotation

Order Catalog No. **PRPCC 13**

Days to Ship **Quotation**

Price **Quotation**

EX Example Press fit (Shininkage)